



Engelmann Heat Cost Allocator

# HCA e2

Heat cost allocators record the heat consumption of the individual radiators in a billing unit (building) and thus enable the individual billing of heat energy per user unit (apartment).



Simple installation due to integrated seal

Storage of all monthly and semi-monthly values over the entire lifetime

Radio transmission times fully customizable to your needs and readout infrastructure

Flexible use due to remote sensor that can be fitted and removed at any time

Seamless integration into the Engelmann system landscape

# Overview

## HCA e2



Flexible in use due to individual setting options for billing and radio transmission parameters. The Engelmann heat cost allocator thus provides you with the basis for future-proof consumption data recording.

The heat cost allocator is a recording device for the consumption-based calculation of heating costs. Unlike a heat meter, for example, it does not measure the amount of heat, but provides dimensionless units that reflect the temporal summation of the temperature difference between the radiator temperature and the room temperature. Ultimately, the individual consumption of the individual users is determined by calculating the ratio of the recording results of all heat cost allocators installed in the billing unit.

The electronic heat cost allocator HCA e2 is fully integrated into the Engelmann system landscape. The consumption data of the installed heat cost allocators are conveniently read out by the respective reception technology used (walk-by or Automatic Meter Reading – AMR). The Engelmann HCA e2 itself provides the basis for flexible adaptation to your individual readout management via its variable radio setup settings. If necessary, the most important data can also be read manually via the high-contrast display.



Even if you are currently still using walk-by readout, the seamless integration into the Engelmann system landscape makes it easy to switch to stationary readout (AMR/gateway), as no adjustments (setup changes) to the heat cost allocator are necessary.

The new integrated seal as well as an extension and deepening of the rear weld stud mount ensure quick and easy assembly.

## Features

- Approved according to EN 834:2013 and compliant with the HKVO
- Type approval: A1.01.2013 according to HKVO
- Storage of 132 monthly and 132 semi-monthly values
- Clip-on remote temperature sensor
- Communication interfaces optical and wireless MBus according to EN 13757-4
  - o AMR (compliant with OMS)
  - o Walk-by readout
- Radio transmission of 15 monthly and 15 semi-monthly values via wireless M-Bus
- Flexibility in encryption mode (Mode 5 / Mode 7) and encryption type (ES master, customer master or individual encryption per device)



Thanks to further development in the area of assembly and installation, which we are constantly making easier and more effective, and the possibility of making the determined consumption data available safely and quickly, regardless of the selected readout technology, the HCA e2 is the first choice for use in your estate.

## General

<b>Device type</b>		2-sensor device; adjustable measuring mode: 2-sensor mode or 1-sensor mode
<b>Estimated lifetime</b>	years	11 + 1
<b>Scaling</b>		unit scale or product scale
<b>Clip-on remote sensor</b>		cable length: 2 m; 5 m
<b>Temperature range</b>	°C	2-sensor mode: 35- 95 (with remote sensor up to 105); 1-sensor mode: 55- 95 (with remote sensor up to 105)
<b>Ambient temperature</b>	°C	-25 – 60
<b>Minimum temperature difference <math>\Delta\theta</math> (counting start of temperature difference)</b>	K	4,5
<b>Interfaces</b>		wireless M-Bus and optical interface (M-Bus protocol)
<b>Display</b>		LCD – 7 digits + special characters
<b>Displayed values</b>		current consumption, billing (due) date, billing date value, checksum
<b>Billing date options</b>		annually variable (except 29.02.); monthly variable (1st - 28th day)
<b>Stored monthly values</b>		132 monthly and 132 semi-monthly values
<b>Measuring free summer months</b>		May-June-July-August-September: freely selectable
<b>Detection of manipulation</b>		break contact
<b>Power supply</b>	V	3; lithium battery
<b>Protection class</b>		IP41 (mounted)

## Wireless M-Bus radio interface (\* factory setting)

<b>Radio protocols</b>		“short telegram” compliant with the OMS (AMR) (current consumption, billing (due) date, billing date value, hint flag); “long telegram” for walk-by readout (factory setting) (current consumption, billing (due) date, billing date value, 15 monthly and 15 semi-monthly values, hint flag)
<b>Transmission power (maximum)</b>	dBm	10
<b>Transmission frequency</b>	MHz	868
<b>Operating modes according to EN 13757-4</b>		S1; T1; C1*
<b>Encryption</b>		AES 128 / Engelmann Master Key*
<b>Start date of radio transmission</b>		annually variable (except 29.02.)
<b>Transmission times (UTC+1)</b>		transmission interval: 2 - 240 min (2 min)* transmission times per day: 12 a.m. - 12 p.m. (8 a.m. - 6 p.m.)* transmission days per week: Mon - Sun (Mon - Sun)* transmission weeks per month: 1 - 4 (1 - 4)* transmission months per year: Jan - Dec (Jan - Dec)*

## Wireless M-Bus radio interface OMS 4 Mode 7 (\* factory setting)

<b>Radio protocols</b>		“short telegram” compliant with the OMS (AMR) (current consumption, billing (due) date, billing date value, hint flag)
<b>Operating modes according to EN 13757-4</b>		T1; C1*
<b>Encryption</b>		AES 128 / individual key per device*
<b>Transmission times (UTC+1)</b>		transmission interval: 2 - 240 min (15 min)* transmission times per day: 12 a.m. - 12 p.m. (12 a.m. - 12 p.m.)* transmission days per week: Mon - Sun (Mon - Sun)* transmission weeks per month: 1 - 4 (1 - 4)* transmission months per year: Jan - Dec (Jan - Dec)*

**Contact us here:**



+49 6222 98 00 188 (Orders)  
+49 6222 98 00 2727 (Technical Service)  
+49 6222 98 00 0 (Head Office)



[info@engelmann.de](mailto:info@engelmann.de)



Engelmann Sensor GmbH  
Rudolf-Diesel-Straße 24-28  
69168 Wiesloch-Baiertal  
Germany



[www.engelmann.de](http://www.engelmann.de)